



**Dongguan Hust Tony Instruments Co.,Ltd**

**东莞华科东尼仪器有限公司**

**Address:** No. 1 Tech 9 Road, High - New Tech Development Zone, Songshan Lake, Dongguan City 523808, China

**Tel:** 86-769-23010657

**Fax:** 86-769-23010667

**Email:** [Addams@tonyhk.hk](mailto:Addams@tonyhk.hk)

## **Static Strength Weights TW-268A/TW-268B-Manufactuer-Hust Tony**



Place standard load on the surface of standing toy or riding toy. Then move the load, measure toy whether there is crack in any accessories, whether they can meet the related standard.

### **Application:**

This weight is mainly used for toy static strength and stability test, toys for the children under 36 months, should use the 25kg weight while toys for the children are 36 month and over should use the 50kg weight. Static strength test of scooter for children weighing more than 20kg should use the 100kg weight.

**Note:** The height of the load's centre of gravity is 150 mm above the seat surface.

### **Technical Specifications**

<b>Model</b>	TW-268A	TW-268B
<b>Net Weight</b>	25±0.2kg	50±0.5kg
<b>Gross Weight</b>	35kg	60kg
<b>Material</b>	Electroplate	

**Standards:** ASTM 963, EN71-1 8.18.1; ISO 8124-1 5.22 Folding or sliding mechanisms